

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

CHANGE WITHOUT NOTICE

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES

COMPACT FIXTURE SUPPORTS WITH VERTICAL OFFSET FITTINGS FOR SIPHON JET WATER CLOSETS




Fig. 0411R
Top View





Fig. 0411D
Top View



Front View

A(Pipe Size) = 4"(100)

- | | |
|--|---|
| | Fig. 0411L CAULK Left Hand |
| | Fig. 0411R CAULK Right Hand |
| | Fig. 0411D CAULK Double |
| | Fig. 0419L CAULK L.H. Long Barrel |
| | Fig. 0419R CAULK R.H. Long Barrel |
| | Fig. 0419D CAULK Double Long Barrel |

Conforms with the requirements of ASME A112.6.1M
up to 500 lbs (227 kg) static live load.

The water closet gasket regularly furnished is made of molded neoprene and designed to fit water closet outlet dimensions and configurations shown in ANSI Standard A112.19.2M-1995, Figure 13B. If gasket is not found to be compatible to fixture due to nonconformance of said fixture to ANSI A112.19.2M, then fixture manufacturer shall be consulted for a suitable gasket recommendation. Jay R. Smith assumes no liability for connections to fixtures which do not conform to these standards.

NOTE: When used with concealed flush valve locate face plate behind supply pipe.

▲ NOTE: Base support must be securely anchored to floor (with four 1/2"(13) bolts provided by contractor).


**© DIMENSION - ADJUS-TO-WALL
TYPE OUTLET CONNECTION**

The Smith Adjus-to-Wall outlet connection provides adjustment at the face of the wall at the time the fixture is set; thus, compensating for wall construction variations. The **©** dimension is measured from the front of the face plate to the finished wall. To properly determine the length of nipple required, deduct 1" (25) from the **©** dimension. The Adjus-to-Wall coupling will provide 1/2" (13) horizontal adjustment in either direction with the coupling extended 5/16" (8) past face of the finished wall.

© dimension = 4" (100) (regularly furnished) consisting of nipple and Adjus-to-Wall coupling permitting adjustment from 3" (76) min. to 4" (100) max.

*ABS (Regularly Furnished) other lengths PVC.

NOTE: Dimensions shown in parentheses are in millimeters.



NIPPLE LENGTHS AVAILABLE

LENGTH	MIN	©	MAX
2 1/2 (64)	2 1/4 (57)	3 1/4 (83)	
*3 1/4 (83)	3 (76)	4 (100)	
*8 1/4 (210)	8 (205)	9 (230)	
10 (255)	9 3/4 (250)	10 3/4 (275)	
12 (305)	11 3/4 (300)	12 3/4 (325)	
15 (380)	14 3/4 (375)	15 3/4 (400)	
18 (455)	17 3/4 (450)	18 3/4 (475)	

NOTE: When nipple lengths between 3 1/4" (83) and 8 1/4" (210) are specified, the 8 1/4" (210) nipple will be supplied. Nipple must be cut to specified length by others.

J H G F	4-16-24 3-18-14 7-1-98 1-26-98	Added ASME Note Revised Dim., Text Submittal Update Added Millimeters	HS TBW ASL EMB	JT CL BS BS	WEIGHT POUNDS	VOLUME CUBIC FEET	FIGURE NUMBER 0411,0419
REV.	DATE	DESCRIPTION	BY	CKD. BY			



WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov